

M30 Collar Opening Specification

The M30MC collar is designed to fit into a rectangular opening. The width of the opening will always be 0.763 inches (19.38 mm). The height of the opening is variable based on the thickness of the material into which the collar is pressed per the table below.

Material Thickness (inches)	Opening Height (inches)
0.025	0.828
0.030	0.833
0.035	0.838
0.040	0.843
0.045	0.849
0.050	0.854
0.055	0.859
0.060	0.864
0.065	0.869
0.070	0.874
0.075	0.879
0.080	0.884
0.085	0.889
0.090	0.894
0.095	0.900
0.100	0.905
0.105	0.910
0.110	0.915
0.115	0.920
0.120	0.925
0.125	0.930