

RRZZHHTTS4-65B-R7 S band (3300-3800M)		Port17	Port18	Port19	Port20	Port21	Port22	Port23	Port24
P0	Full Power_Broadcast_65 deg for tilt 2-5	Amp(voltage)	1	1	1	1	0	0	0
		Phz	6.3	67.6	68.5	0	0	0	0
P1	Full Power_Broadcast_65 deg for tilt 2-5	Amp(voltage)	0	0	0	0	1	1	1
		Phz	0	0	0	0	231.8	0	159.1
P0	Full Power_Broadcast_65 deg for tilt 6-8	Amp(voltage)	1	1	1	1	0	0	0
		Phz	16.7	79	57.7	0	0	0	0
P1	Full Power_Broadcast_65 deg for tilt 6-8	Amp(voltage)	0	0	0	0	1	1	1
		Phz	0	0	0	0	239	0	159.4
P0	Full Power_Broadcast_65 deg for tilt 9-12	Amp(voltage)	1	1	1	1	0	0	0
		Phz	36.2	97.1	61	0	0	0	0
P1	Full Power_Broadcast_65 deg for tilt 9-12	Amp(voltage)	0	0	0	0	1	1	1
		Phz	0	0	0	0	242.9	0	142.6

RRZZHHTTS4-65B-R7 S band (3300-3800M)		Port17	Port18	Port19	Port20	Port21	Port22	Port23	Port24
+45	Service Beam_0deg for tilt2-5	Amp(voltage)	1	0	1	0	1	0	1
		Phz	6.2	0	0.5	0	4.1	0	0
-45	Service Beam_0deg for tilt2-5	Amp(voltage)	0	1	0	1	0	1	0
		Phz	0	6.2	0	0.5	0	4.1	0
+45	Service Beam_0deg for tilt6-8	Amp(voltage)	1	0	1	0	1	0	1
		Phz	20.2	0	0	0	18.9	0	1.4
-45	Service Beam_0deg for tilt6-8	Amp(voltage)	0	1	0	1	0	1	0
		Phz	0	20.2	0	0	0	18.9	0
+45	Service Beam_0deg for tilt9-12	Amp(voltage)	1	0	1	0	1	0	1
		Phz	30.8	0	2.1	0	31.5	0	0
-45	Service Beam_0deg for tilt9-12	Amp(voltage)	0	1	0	1	0	1	0
		Phz	0	30.8	0	2.1	0	31.5	0

RRZZHHTTS4-65B-R7 S band (3300-3800M)		Port17	Port18	Port19	Port20	Port21	Port22	Port23	Port24
+45	Service Beam_30deg for tilt2-5	Amp(voltage)	1	0	1	0	1	0	1
		Phz	0	0	102.7	0	197.7	0	295.6
-45	Service Beam_30deg for tilt2-5	Amp(voltage)	0	1	0	1	0	1	0
		Phz	0	0	0	102.7	0	197.7	0
+45	Service Beam_30deg for tilt6-8	Amp(voltage)	1	0	1	0	1	0	1
		Phz	0	0	91.4	0	192.1	0	284.6
-45	Service Beam_30deg for tilt6-8	Amp(voltage)	0	1	0	1	0	1	0
		Phz	0	0	0	91.4	0	192.1	0
+45	Service Beam_30deg for tilt9-12	Amp(voltage)	1	0	1	0	1	0	1
		Phz	0	0	84.6	0	195.9	0	272.2
-45	Service Beam_30deg for tilt9-12	Amp(voltage)	0	1	0	1	0	1	0
		Phz	0	0	0	84.6	0	195.9	0

RRZZHHTTS4-65B-R7 S band (3300-3800M)		Port17	Port18	Port19	Port20	Port21	Port22	Port23	Port24
+45	Service Beam_-30deg for tilt2-5	Amp(voltage)	1	0	1	0	1	0	1
		Phz	309.6	0	204.7	0	120.4	0	0
-45	Service Beam_-30deg for tilt2-5	Amp(voltage)	0	1	0	1	0	1	0
		Phz	0	309.6	0	204.7	0	120.4	0
+45	Service Beam_-30deg for tilt6-8	Amp(voltage)	1	0	1	0	1	0	1
		Phz	306.9	0	195.1	0	128.2	0	0
-45	Service Beam_-30deg for tilt6-8	Amp(voltage)	0	1	0	1	0	1	0
		Phz	0	306.9	0	195.1	0	128.2	0
+45	Service Beam_-30deg for tilt9-12	Amp(voltage)	1	0	1	0	1	0	1
		Phz	323.1	0	193.4	0	138.6	0	0
-45	Service Beam_-30deg for tilt9-12	Amp(voltage)	0	1	0	1	0	1	0
		Phz	0	323.1	0	193.4	0	138.6	0

RRZZHHTTS4-65B-R7 S band (3300-3800M)		Port17	Port18	Port19	Port20	Port21	Port22	Port23	Port24
+45	Service Beam_-30deg for tilt2-5	Amp(voltage)	1	0	1	0	1	0	1
		Phz	309.6	0	204.7	0	120.4	0	0
-45	Service Beam_-30deg for tilt2-5	Amp(voltage)	0	1	0	1	0	1	0
		Phz	0	309.6	0	204.7	0	120.4	0
+45	Service Beam_-30deg for tilt6-8	Amp(voltage)	1	0	1	0	1	0	1
		Phz	306.9	0	195.1	0	128.2	0	0
-45	Service Beam_-30deg for tilt6-8	Amp(voltage)	0	1	0	1	0	1	0
		Phz	0	306.9	0	195.1	0	128.2	0
+45	Service Beam_-30deg for tilt9-12	Amp(voltage)	1	0	1	0	1	0	1
		Phz	323.1	0	193.4	0	138.6	0	0
-45	Service Beam_-30deg for tilt9-12	Amp(voltage)	0	1	0	1	0	1	0
		Phz	0	323.1	0	193.4	0	138.6	0

RRZZHHTTS4-65B-R7 S band (3300-3800M)		Port17	Port18	Port19	Port20	Port21	Port22	Port23	Port24
+45	Soft Split_24deg for tilt2-5	Amp(voltage)	0.53	0	1	0	1	0	0.53
		Phz	0	0	74.4	0	157.9	0	235.5
-45	Soft Split_24deg for tilt2-5	Amp(voltage)	0	0.53	0	1	0	1	0
		Phz	0	0	0	74.4	0	157.9	0
+45	Soft Split_24deg for tilt6-8	Amp(voltage)	0.53	0	1	0	1	0	0.53
		Phz	0	0	77.4	0	170.4	0	237.9
-45	Soft Split_24deg for tilt6-8	Amp(voltage)	0	0.53	0	1	0	1	0
		Phz	0	0	0	77.4	0	170.4	0
+45	Soft Split_24deg for tilt9-12	Amp(voltage)	0.53	0	1	0	1	0	0.53
		Phz	0	0	54.6	0	162.7	0	214
-45	Soft Split_24deg for tilt9-12	Amp(voltage)	0	0.53	0	1	0	1	0
		Phz	0	0	0	54.6	0	162.7	0

RRZZHHTTS4-65B-R7 S band (3300-3800M)		Port17	Port18	Port19	Port20	Port21	Port22	Port23	Port24
+45	Soft Split_-24deg for tilt2-5	Amp(voltage)	0.53	0	1	0	1	0	0.53
		Phz	244.2	0	160.5	0	91.9	0	0
-45	Soft Split_-24deg for tilt2-5	Amp(voltage)	0	0.53	0	1	0	1	0
		Phz	0	244.2	0	160.5	0	91.9	0
+45	Soft Split_-24deg for tilt6-8	Amp(voltage)	0.53	0	1	0	1	0	0.53
		Phz	266.3	0	160.1	0	102.2	0	0
-45	Soft Split_-24deg for tilt6-8	Amp(voltage)	0	0.53	0	1	0	1	0
		Phz	0	266.3	0	160.1	0	102.2	0
+45	Soft Split_-24deg for tilt9-12	Amp(voltage)	0.53	0	1	0	1	0	0.53
		Phz	276.2	0	159.2	0	114.8	0	0
-45	Soft Split_-24deg for tilt9-12	Amp(voltage)	0	0.53	0	1	0	1	0
		Phz	0	276.2	0	159.2	0	114.8	0