

E02563-000 | FPS-OCM-I-0



FPS-OCM Front patching shelf, 19" (4RU) without storage basket, for holding up to 12 OCM1 or 24 OCMF optical modules

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	CommScope®
Product Type	Fiber VAM panel
Product Series	FPS

General Specifications

Application	Accommodates LGX type modules in a rack environment
Color	Gray
Interface, front	Unloaded
Patch Cord Routing	Left sided Right sided
Rack Type	EIA 19 in
Rack Units	4
Total Ports, quantity	0

Dimensions

Height	173 mm 6.811 in
Width	481 mm 18.937 in
Depth	279 mm 10.984 in

Material Specifications

Finish	Powder coated
---------------	---------------

Packaging and Weights

Included	Label
Packaging quantity	1

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

