

FGS-HTBK-18-5-32PC



FiberGuide® 18in Horizontal Tool-less Bracket Kit for 4x12 and 4x18in Systems, Kit of 32

This 18in bracket attaches to 18in ladder rack using our tool-less Quick Knobs. Used to mount and support 4x12 and 4x18in FiberGuide® above ladder racking. Ships in a kit of 32 brackets.

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Support mounting kit
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Black
Note	Includes fastening hardware
Orientation	Horizontal
Section Type	Bracket

Dimensions

Height	171.501 mm 6.752 in
Width	114.3 mm 4.5 in
Length	460.096 mm 18.114 in
System Dimensions	102 mm x 305 mm (4 in x 12 in) 102 mm x 457 mm (4 in x 18 in)

Packaging and Weights

Packaging quantity	32
Weight, net	35.025 kg 77.216 lb

Included Products

HDW-12021 - FiberGuide® Quick Knob with T-Bolt

HDW-12021



FiberGuide® Quick Knob with T-Bolt

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber raceway hardware
Product Brand	FiberGuide®
Product Series	FGS
Minimum Order Quantity	10

General Specifications

Color	Black
Orientation	Horizontal
Section Type	Accessory

Dimensions

System Dimensions	102 mm x 102 mm (4 in x 4 in) 102 mm x 152 mm (4 in x 6 in) 102 mm x 305 mm (4 in x 12 in) 102 mm x 610 mm (4 in x 24 in) 51 mm x 152 mm (2 in x 6 in)
--------------------------	--

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Packaging quantity	1
Weight, net	0.015 kg 0.033 lb

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

HDW-12021

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

