760249464 | OFDC-B8G-L2/G0-NN-N-72



OFDC B8G Fiber Optic Splice/Patch Closure, Gel Cable sealing, 6 preinstalled 12 fiber trays , 8 duplex LC/APC adapters, no splitter

- Advanced gel sealing technology ensures fast and easy field handling without a need for special tools
- Individual access to drop cable connection area and seperate zones for looped cable storage for most cable types
- Compact and modular design suited for wraparound drop cable installation, enabling faster deployments
- Allows easy pass-through cabling and integration of optical components, even at later deployment stages

Product Classification

Length

Regional Availability	EMEA	
Product Type	Single-ended, rectangular fiber closure	
Product Series	OFDC	
General Specifications		
Cable Ports Quantity, total	4 round ports + 8 multi-out ports (16 cables)	
Cable Sealing Type	Compressed gel	
Closure Sealing Type	Hinged with latch	
Closure Style	Single-ended	
Color	Black	
Mounting	Manhole Pedestal Strand Wall	
Port Type	LC/APC	
Splice Tray Included, quantity	6	
Splice Tray Type Included	12-way, heat shrink	
Splitter Type	No splitter	
Splitter, quantity	0	
Dimensions		
Height	128 mm 5.039 in	
Width	156 mm 6.142 in	

Page 1 of 3


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2024

324 mm | 12.756 in



760249464 | OFDC-B8G-L2/G0-NN-N-72

Ordering Tree



Material Specifications

Material Type

Rugged polymer

Environmental Specifications

Installation temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Relative Humidity	93%, non-condensing
Environmental Space	Above ground Below ground
Qualification Standards	IEC 60529, IP68 + 2 m waterhead
UV Resistance	UV stabilized

Packaging and Weights

Packaging quantity	1	
Packaging Type	Box	Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2024



760249464 | OFDC-B8G-L2/G0-NN-N-72

ROHS

UK-ROHS

Compliant Compliant



Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2024

