760249553 | FT-MP-6A-LW-25



Field Term Modular Plug, RJ45, Cat6A, Large Wire (25 ea/pkg)

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Portfolio CommScope®

Product Type Modular plug

General Specifications

ANSI/TIA Category 6A

Cable Type U/UTP (unshielded)

Color Clear

Conductor Type Solid | Stranded

Interface RJ45

Positions/Loaded Contacts 8

Termination Type IDC

Dimensions

Compatible Cable Diameter, maximum 7.3 mm | 0.287 in

Compatible Cable Diameter, minimum 7.1 mm | 0.28 in

Compatible Insulated Conductor Diameter, maximum 1.03 mm | 0.041 in

Compatible Insulated Conductor Diameter, minimum 0.9 mm | 0.035 in

Contact Plating Thickness 1.27 µm

Compatible Conductor Gauge, solid 23 AWG | 24 AWG

Material Specifications

Contact Base Material Copper alloy

Contact Plating Material Gold over nickel



Page 1 of 2

760249553 | FT-MP-6A-LW-25

Material Type Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Relative HumidityUp to 93%, non-condensing

Safety Standard UL 114344

Packaging and Weights

Packaging quantity25Packaging TypeBag

