

Optical Passives (ISP)

OP34S4S

Scalable 4x4 Optical Splitter/Combiner


FEATURES

- Maximum flexibility for configuration of splitter/combiner functions
- Low insertion loss
- Dual operating wavelength windows (1310 nm and 1550 nm)
- High port-to-port uniformity
- SC/APC connectors ensure performance repeatability, compatibility and easy installation and maintenance
- Removable connectors for easy cleaning
- High packaging density (up to 32 modules per chassis)



PRODUCT OVERVIEW


The ARRIS unique scalable 4x4 splitter/combiner module provides optimum versatility in minimum rack space to meet a variety of network configuration requirements for optical splitting and combining functions. When fully loaded, ARRIS's CH3000 chassis holds 32 half-depth modules; its packaging concept also permits mounting in any standard LGX chassis. How the module can be configured for the combining and splitting of broadcast and narrowcast signals is shown on the following page.



SPECIFICATIONS

Characteristics	Specification
Physical	
Dimensions	6.5" D x 4.3" H x 1.0" W (3RU) (17 cm x 11 cm x 2.5 cm)
Weight	0.8 lbs (0.34 kg)
Environmental	
Operating Temperature Range	-20°C to +65°C (-4°F to +149°F)
Storage Temperature Range	-40°C to +85°C (-40°F to +185°F)
Humidity	5% to 95% non-condensing
Optical	
Optical connectors	SC/APC
Number of splitters	1
Splitter type	4x4
Operating wavelength	Dual windows (1263.5–1357.5 nm and 1423.5–1617.5 nm)
Directivity, min	55 dB
Return loss, min	55 dB (including connectors)
Power handling at input port, max	27 dBm
Uniformity, max (typical)	0.6 (0.3) dB
Spectral flatness, max (typical)	0.6 (0.3) dB
Polarization dependent loss, max	0.2 dB
Insertion loss including connectors, max (typical)	
1 x 2 splitter	3.6 (3.3) dB
1 x 4 splitter	6.8 (6.4) dB

ORDERING INFORMATION



Optical Passive Module
(Scalable 4x4 Optical Splitter/Combiner)

AS = SC/APC Connector

RELATED PRODUCTS

CH3000 Chassis	Optical Patch Cords
Optical Transmitters	Optical Passives
HPON™	Installation Services

Customer Care

Contact Customer Care for product information and sales:

- United States: 866-36-ARRIS
- International: +1-678-473-5656

Note: Specifications are subject to change without notice.

Copyright Statement: ©ARRIS Enterprises, LLC, 2016. All rights reserved. No part of this publication may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from ARRIS Enterprises, LLC ("ARRIS"). ARRIS reserves the right to revise this publication and to make changes in content from time to time without obligation on the part of ARRIS to provide notification of such revision or change. ARRIS and the ARRIS logo are registered trademarks of ARRIS Enterprises, LLC. Other trademarks and trade names may be used in this document to refer to either the entities claiming the marks or the names of their products. ARRIS disclaims proprietary interest in the marks and names of others. The capabilities, system requirements and/or compatibility with third-party products described herein are subject to change without notice.