



HGS620 Keystone Adapter, Black (25 ea/pkg)

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Adapter kit
<b>Ordering Note</b>	Minimum order quantity, 20 packs

## General Specifications

**Color** Black

## Dimensions

**Height** 3.56 mm | 0.14 in

**Width** 12.7 mm | 0.5 in

**Depth** 21.84 mm | 0.86 in

## Material Specifications

**Material Type** High-impact, flame retardant, thermoplastic

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Flammability Rating** UL 94 V-0

**Safety Standard** UL | cUL

## Packaging and Weights

**Packaging quantity** 25

## Regulatory Compliance/Certifications

**Agency**

CHINA-ROHS  
ISO 9001:2015  
REACH-SVHC  
ROHS  
UK-ROHS

**Classification**

Below maximum concentration value  
Designed, manufactured and/or distributed under this quality management system  
Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)  
Compliant  
Compliant

