

C300-NMTR-1M

CNT-300A CNT® Jumper with interface types N Male and TNC Male
Right Angle, 1m



Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-300

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	CNT-400
Interface, Connector A	N Male
Interface, Connector B	TNC Male
Specification Sheet Revision Level	A

Dimensions

Length	1 m 3.281 ft
Nominal Size	0.300 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–2000 MHz	1.288	18
2000–3000 MHz	1.433	14.99

Jumper Assembly Sample Label

C300-NMTR-1M



Included Products

- 300BPNM-C – Type N Male for CNT-300 braided cable
- 300BPTR-C – TNC Male Right Angle for CNT-300 braided cable
- CNT-300A – CNT-300, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket