

# CPC3392

---



## GigaSPEED XL® Cat 6 Patch Cord, LSZH

### Product Classification

**Regional Availability**

Asia | Australia/New Zealand | EMEA | Latin America | North America

**Portfolio**

SYSTIMAX®

**Product Type**

Twisted pair patch cord

**Product Brand**

GigaSPEED XL®

**Product Series**

CPC | UTG

**Ordering Note**

Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords | Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices

### General Specifications

**ANSI/TIA Category**

6

**Cable Type**

U/UTP (unshielded)

**Conductor Type**

Stranded

**Interface, Connector A**

RJ45 plug

**Interface Feature, connector A**

Standard

**Interface, Connector B**

RJ45 plug

**Interface Feature, connector B**

Standard

**Jacket Color**

Black | Blue | Dark gray | Light blue | Lilac | Orange | Red | Spring green | White | Yellow

**Pairs, quantity**

4

**Transmission Standards**

IEEE 802.3bt Type 4

**Wiring**

T568B

### Dimensions

# CPC3392

---

<b>Cable Assembly Length Range (m)</b>	1 – 30
<b>Cable Assembly Length Range (ft)</b>	1 – 100
<b>Cable Assembly Length Range (cm)</b>	15 – 999
<b>Cable Assembly Length Range (in)</b>	6 – 999
<b>Diameter Over Jacket</b>	6.02 mm   0.237 in
<b>Compatible Conductor Gauge, stranded</b>	24 AWG   24 AWG

## Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

## Electrical Specifications

<b>dc Resistance, maximum</b>	0.3 ohm
<b>Safety Voltage Rating</b>	300 V

## Ordering Tree

# CPC3392

CPC     - <sup>9</sup> <sup>10</sup> <sup>11</sup> <sup>12</sup>

## Outlet Color

9	0	Not applicable
	1	Black
	2	Blue
	3	Gray
	4	Green
	5	Ivory
	6	Orange
	7	Red
	8	White
	9	Yellow
	B	Lilac

## Jacket Color

10	1	Black
	2	Light blue
	3	Dark gray
	4	Spring green
	5	Ivory
	6	Orange
	7	Red
	8	White
	9	Yellow
	B	Lilac
	C	Gray
	K	Pink
	L	Violet
	M	Green
	Z	Blue

## UOM

11	F	Foot
	M	Meter
	N	Inch
	C	Centimeter

## Length

12	XXX
----	-----

## Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

## Material Specifications

### Contact Plating Material

Precious metals

### Material Type

Copper alloy | Polycarbonate

## Mechanical Specifications

### Plug Insertion Life, minimum

750 times

### Plug Retention Force, minimum

133 N | 29.9 lbf

## Environmental Specifications

### Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

### Environmental Space

Low Smoke Zero Halogen (LSZH)

### Flammability Rating

UL 94 V-0

## Packaging and Weights

### Packaging quantity

1

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system

# CPC3392

---

