

# T-10-43-M

Termination Load, 0–3000 MHz, Not for PIM-rated applications



## OBSOLETE

This product was discontinued on: December 31, 2019

### Replaced By:

T-10-UW-43-M

Termination Load, 0–6000 MHz, Not for PIM-rated applications

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Product Type

Termination Load

## General Specifications

### Device Type

Termination Load

### Application

Indoor/Outdoor

### Color

Black

### Inner Contact Plating

Silver

### Interface

4.3-10 Male

### Outer Contact Plating

Trimetal

## Dimensions

### Length

64 mm | 2.52 in

### Diameter, maximum

35 mm | 1.378 in

## Electrical Specifications

### Return Loss, minimum

23 dB

### Average Power, maximum

10 W

### Impedance

50 ohm

# T-10-43-M

---

<b>Operating Frequency Band</b>	0 – 3000 MHz
<b>VSWR</b>	1.15

## Environmental Specifications

<b>Operating Temperature</b>	-35 °C to +50 °C (-31 °F to +122 °F)
<b>Relative Humidity</b>	Up to 100%
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP65

## Packaging and Weights

<b>Height, packed</b>	53 mm   2.087 in
<b>Width, packed</b>	58 mm   2.283 in
<b>Length, packed</b>	98 mm   3.858 in
<b>Weight, gross</b>	0.14 kg   0.309 lb
<b>Weight, net</b>	0.12 kg   0.265 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted

