

T-10-NF



Termination Load, 0–3000 MHz

OBSOLETE

This product was discontinued on: December 31, 2019

Replaced By:

T-10-UW-NF

Termination Load, 0–6000 MHz, Not for PIM-rated applications

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Termination Load

General Specifications

Device Type	Termination Load
Application	Indoor/Outdoor
Color	Black
Inner Contact Plating	Silver
Interface	N Female
Outer Contact Plating	Trimetal

Dimensions

Length	53.5 mm 2.106 in
Diameter, maximum	35 mm 1.378 in

Electrical Specifications

Return Loss, minimum	23 dB
Average Power, maximum	10 W
Impedance	50 ohm
Operating Frequency Band	0 – 3000 MHz
VSWR	1.15

T-10-NF

Environmental Specifications

Operating Temperature	-35 °C to +50 °C (-31 °F to +122 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	68 mm 2.677 in
Width, packed	53 mm 2.087 in
Length, packed	58 mm 2.283 in
Volume	209 mm ³ 0.013 in ³
Weight, gross	0.12 kg 0.265 lb
Weight, net	0.1 kg 0.22 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

