


# 860633312

---



MPO8, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber connector   |
| <b>Product Brand</b>         | LazrSPEED®  |

## General Specifications

|                          |              |
|--------------------------|--------------|
| <b>Color</b>             | Lime green   |
| <b>Color, boot</b>       | Gray         |
| <b>Ferrule Geometry</b>  | Flat         |
| <b>Interface</b>         | MPO/UPC Male |
| <b>Interface Feature</b> | Pinned       |
| <b>Total Fiber Count</b> | 8            |

## Dimensions

|                                  |                    |
|----------------------------------|--------------------|
| <b>Length</b>                    | 60.1 mm   2.366 in |
| <b>Compatible Cable Diameter</b> | 3 mm   0.118 in    |

## Material Specifications

|                         |         |
|-------------------------|---------|
| <b>Ferrule Material</b> | Polymer |
|-------------------------|---------|

## Mechanical Specifications

|  |                |
|--|----------------|
| <b>Cable Retention Strength, maximum</b> | 11.24 lb @ 0 ° |
|--|----------------|

## Optical Specifications

|                                      |                          |
|--------------------------------------|--------------------------|
| <b>Fiber Mode</b>                    | Multimode                |
| <b>Fiber Type</b>                    | OM5, LazrSPEED® wideband |
| <b>Insertion Loss Change, mating</b> | 0.3 dB                   |

# 860633312

---

|   |                  |
|---|------------------|
| <b>Optical Components Standard</b>        | ANSI/TIA-568-C.3 |
| <b>Insertion Loss Change, temperature</b> | 0.3 dB           |
| <b>Insertion Loss, maximum</b>            | 0.2 dB           |
| <b>Return Loss, minimum</b>               | 27 dB            |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant  |



## \* Footnotes

|   |   |
|---|---|
| <b>Insertion Loss Change, mating</b>      | TIA-568: Maximum insertion loss change after 500 matings                |
| <b>Insertion Loss Change, temperature</b> | Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F) |