

CX3399760 | 1250110 EMPTY DUCT COEX

ConQuest® Empty Conduit, 1 1/4 in, SDR 11, orange



Product Classification

Product Type	Empty conduit
Product Brand	ConQuest®

General Specifications

Color	Orange
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Length	914.4 m 3000 ft
Inner Diameter, nominal	33.985 mm 1.338 in
Outer Diameter, nominal	42.164 mm 1.66 in
Wall Thickness Designation	SDR 11
Wall Thickness, minimum	3.835 mm 0.151 in
Nominal Size	1-1/4 in

Material Specifications

Flexural Modulus, minimum	551.581 N/mm ² 80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated

CX3399760 | 1250110 EMPTY DUCT COEX

Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported	457.2 mm 18 in
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	20.684 N/mm ² 3000 psi
Pulling Tension, maximum	689.46 kg 1520 lb

Environmental Specifications

Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net	476.212 kg/km 320 lb/kft
--------------------	----------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance