FGS-FLEXV-4F-A2C



FiberGuide® FlexVertical Dual Kit, 4x4 to Dual 2x2in, 4ft Length, Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Drop kit
Product Brand FiberGuide®

Product Series FGS

General Specifications

Product Feature Snap-together design

Angle/Bend Direction 30°

Color Yellow

Orientation Vertical

Section Type Vertical section

Dimensions

 Height
 1,447.038 mm | 56.97 in

 Width
 107.95 mm | 4.25 in

 Length
 172.618 mm | 6.796 in

System Dimensions 102 mm x 102 mm (4 in x 4 in) | 51 mm x 51 mm (2 in x 2 in)

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0
Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

COMMSCOPE®

FGS-FLEXV-4F-A2C

Packaging and Weights

Included Hardware

Weight, net 1.795 kg | 3.957 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

