

FGS-HTHR-12MM-75CM



FiberGuide® Threaded Rod, 12mm Diameter, 75cm Length

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Threaded rod
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Silver
Orientation	Horizontal
Section Type	Mounting

Dimensions

Length	mm 29.528 in
Rod Length	750 mm 29.528 in
Thread Size	12 mm
System Dimensions	102 mm x 102 mm (4 in x 4 in) 102 mm x 152 mm (4 in x 6 in) 51 mm x 152 mm (2 in x 6 in)

Ordering Tree

FGS-HTHR-12MM-75CM

FGS - HTHR - $\overset{9}{\boxed{5/8}}$ - $\overset{10}{\boxed{72}}$

Rod Diameter

9	1/2	1/2 in
	5/8	5/8 in
	12 MM	12 mm
	14 MM	14 mm
	16 MM	16 mm

Rod Length

10	12	12 in
	30	30 in
	48	48 in
	72	72 in
	30CM	30 cm
	75CM	75 cm
	180CM	180 cm

* Rod diameter and length needs to be both metric or imperial sized

Packaging and Weights

Weight, net 0.077 kg | 0.17 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

