


FGS-MD4E-H



FiberGuide® 45° Down Elbow, 4x24in, Yellow

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Elbow
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Angle/Bend Direction	45° down
Color	Yellow
Orientation	Horizontal
Section Type	Elbow section

Dimensions

Height	117 mm 4.606 in
Width	647 mm 25.472 in
System Dimensions	102 mm x 610 mm (4 in x 24 in)

Ordering Tree

FGS-MD4E-H



Section Color

9	empty	yellow
	B	black

Section Size

10	A	4 x 4 in
	B	4 x 6 in
	C	2 x 2 in*
	F	4 x 12 in
	G	2 x 6 in
	H	4 x 24 in

* FGS-MD4A-C or FGSB-MD4A-C

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 1.583 kg | 3.49 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

