

FGS-MH9E-B



FiberGuide® 90° Horizontal Elbow, 4x6in, Yellow

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Elbow
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Angle/Bend Direction	90°
Color	Yellow
Orientation	Horizontal
Section Type	Elbow section

Dimensions

Height	112 mm 4.409 in
Width	152 mm 5.984 in
Length	288 mm 11.339 in
System Dimensions	102 mm x 152 mm (4 in x 6 in)

Ordering Tree

FGS-MH9E-B



Section Color

9	empty	yellow
	B	black

Section Size

1	A	4 x 4 in
0	B	4 x 6 in
	F	4 x 12 in
	F-VS	4 x 12 in , variable support bracket
	G	2 x 6 in
	M	4 x 18 in

* Support brackets only come in black

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 0.509 kg | 1.122 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

