

204679A-5



Boot Assembly, 4 in, for 1/2 in corrugated coaxial cable

OBSOLETE

Replaced By:

SEC-412

SnapSeal™ Entry Cushion with 4 holes for 1/2 in corrugated coaxial cable

Product Classification

Product Type	Boot assembly
Ordering Note	CommScope® non-standard product

General Specifications

Cable Type	Corrugated
Cables per Cushion	1
Color	Black

Dimensions

Height	101.6 mm 4 in
Length	76.2 mm 3 in
Nominal Size	1/2 in

Material Specifications

Material Type	EPDM rubber
----------------------	-------------

Environmental Specifications

UV Resistance Test Method	MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation	≥1000 hours

204679A-5

Weather Resistance Test Method

04AS00-03.9.0 | IEC 60529:2001, IP66

Packaging and Weights

Height, packed

149.86 mm | 5.9 in

Width, packed

149.86 mm | 5.9 in

Length, packed

78.74 mm | 3.1 in

Included

Boot | Cushion | Two clamps

Packaging quantity

1

Weight, gross

0.64 kg | 1.411 lb

Regulatory Compliance/Certifications

Agency**Classification**

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant