



TENIO™ Splice Tray for small closures (B6 size) for up to 12 ANT splice protectors

- Fiber and cable technology independent
- Compatible with G652.D optical fiber

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America
Product Type	Fiber splice tray
Product Series	TENIO

General Specifications

Color	Gray
Splice Tray Chip Type	ANT
Splice Tray Included, quantity	1
Splices per Tray, quantity	12

Dimensions

Splice Protector Length, maximum	35 mm 1.378 in
Splice Protector Length, minimum	25 mm 0.984 in

Material Specifications

Material Type	PBT PET
----------------------	-----------

Mechanical Specifications

Minimum Bend Radius, standard	30 mm 1.181 in
--------------------------------------	------------------

Environmental Specifications

Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Outdoor

Packaging and Weights

760239564 | TENIO-B6-TRAY-A12

Packaging quantity	12
Packaging Type	Bag Carton
Weight, net	0.1 kg 0.22 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

