



CWPT wraparound repair sleeve heat shrink kit, unpressurized, for 15 to 84 mm cable diameter, 880 mm long

- Excellent split resistance of the composite structure offers superior resistance to mechanical abuse during and after the installation
- Integrated moisture barrier completely reconstitutes the cable sheath construction

## OBSOLETE

This product was discontinued on: June 30, 2022

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Heat shrink repair sleeve
<b>Product Series</b>	CWPT

## General Specifications

<b>Color</b>	Black
<b>Sealant Type</b>	Hotmelt adhesive

## Dimensions

<b>Length</b>	880 mm   34.646 in
<b>Expanded Inside Diameter, minimum</b>	84 mm   3.307 in
<b>Recovered Inside Diameter, maximum</b>	15 mm   0.591 in
<b>Single Cable Diameter, maximum</b>	84 mm   3.307 in
<b>Single Cable Diameter, minimum</b>	15 mm   0.591 in
<b>Expanded Wall Thickness, minimum</b>	1.1 mm   0.043 in

## Material Specifications

<b>Material Type</b>	Fiber-reinforced multi-layer sealing sleeve
----------------------	---

## Environmental Specifications

# 860634384 | CWPT-84/15-880-N

---

**Environmental Space**                      Aerial | Buried | Ducted

## Packaging and Weights

**Packaging quantity**                      1

**Packaging Type**                          Bag | Carton