

244106A-48



Flex-Twist Hanger Assembly for WR187

Product Classification

Product Type Hanger kit

General Specifications

Cable Type Elliptical waveguide

Cables per Hanger 1

Color Silver

Hanger Type Flex-Twist hanger

Mounting 4.5 in OD pipe

Dimensions

Height 387.4 mm | 15.252 in

Width 82.6 mm | 3.252 in

Length 387.4 mm | 15.252 in

Waveguide Size WR187 | WG12 | R48

Material Specifications

Material Type Stainless steel

Mechanical Specifications

Wind Speed, survival with 1/2 in (12 mm) radial ice 201.167 km/h | 125 mph

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Test Method MIL-F-14072C | MIL-STD-889B

Packaging and Weights

Included Clamp | Rubber grommet | Threaded rod

244106A-48

Packaging quantity 1
Weight, gross 0.68 kg | 1.499 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system