



Cushion Hanger Assembly for 7/8 in corrugated coaxial cable, three holes

OBSOLETE

Product Classification

Product Type	Hanger kit
Product Brand	I-Line
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	3
Color	Black
Hanger Type	Cushion hanger
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Height	25.4 mm 1 in
Width	79.8 mm 3.142 in
Length	96 mm 3.78 in
Compatible Diameter, maximum	31 mm 1.22 in
Compatible Diameter, minimum	26.7 mm 1.051 in
Nominal Size	7/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

294657

Material Specifications

Material Type Engineered plastic

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 17 cm | 6.693 in

Width, packed 13 cm | 5.118 in

Length, packed 10 cm | 3.937 in

Packaging quantity 10

Weight, gross 0.44 kg | 0.97 lb