



Crimping Tool for CNT-300 and CNT-400 connectors

Product Classification

Product Type	Tool
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications

Application	Crimps the ferrule for CNT® connectors
Tool Type	Crimp tool

Dimensions

Crimp Die Diameter	10.16 mm 0.4 in 7.62 mm 0.3 in
Wrench Opening	0 mm 0 in

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Torque Value	0 in lb 0 N-m
---------------------	-----------------

Packaging and Weights

Height, packed	20.32 mm 0.8 in
Width, packed	99.06 mm 3.9 in
Length, packed	279.4 mm 11 in
Packaging quantity	1
Weight, gross	0.66 kg 1.455 lb

Regulatory Compliance/Certifications

Agency	Classification
---------------	-----------------------

CTBC

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

