

# EM1612-001 | SCIL-B-TRAY-48-KIT-S

---

SCIL-B 48-fiber splice tray kit for splice closure, 48 SMOUV protectors included

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Product Type</b>          | Fiber splice tray   |
| <b>Product Brand</b>         | SCIL™   |
| <b>Product Series</b>        | SCIL-B  |

## General Specifications

|                                       |   |
|---------------------------------------|---|
| <b>Application</b>                    | For use with SCIL-B Fiber splice closures |
| <b>Color</b>                          | Gray                                      |
| <b>Splice Tray Chip Type</b>          | Heat shrink                               |
| <b>Splice Tray Included, quantity</b> | 2   |
| <b>Splices per Tray, quantity</b>     | 24  |

## Material Specifications

|                      |           |
|----------------------|-----------|
| <b>Material Type</b> | PBT   PET |
|----------------------|-----------|

## Environmental Specifications

|                            |         |
|----------------------------|---------|
| <b>Environmental Space</b> | Outdoor |
|----------------------------|---------|

## Packaging and Weights

|                           |                              |
|---------------------------|------------------------------|
| <b>Included</b>           | SMOUV splice protectors (48) |
| <b>Packaging quantity</b> | 1                            |
| <b>Packaging Type</b>     | Bag   Carton                 |
| <b>Weight, net</b>        | 0.1 kg   0.22 lb             |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |

