

# FD3-AC072J00JABP1B

---



FDH 3000 Fiber Distribution Extra Small Cabinet, 72F, SC/APC, no splitters, dielectric loose tube, 100 ft, 12F

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber distribution hub
<b>Product Series</b>	FDH 3000

## General Specifications

<b>Access</b>	Front
<b>Cable Type</b>	Dielectric - Loose Tube
<b>Color</b>	Putty white
<b>Distribution Cables, quantity</b>	1
<b>Distribution Ports, quantity</b>	144
<b>Fibers per Distribution Cable, quantity</b>	72
<b>Fibers per Feeder Cable, quantity</b>	12
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Mounting</b>	Pole
<b>Splitter Slots, quantity</b>	9

## Dimensions

<b>Height</b>	762 mm   30 in
<b>Width</b>	533 mm   20.984 in
<b>Depth</b>	356 mm   14.016 in
<b>Cable Length</b>	30.48 m   100 ft
<b>Enclosure Size</b>	Extra small

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

# FD3-AC072J00JABP1B

---

## Environmental Specifications

**Environmental Space** Aerial

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

