## MS-100-SSH



Tapered Pipe-to-Pipe Adapter, adapts 1-1/2 in to 3-1/2 in OD pipe to 4 in to 9 in OD pipe

#### **Product Classification**

Product Type Adapter

General Specifications

MountingPipe-to-pipeTower TaperTapered

**Dimensions** 

 Height
 50.8 mm | 2 in

 Width
 304.8 mm | 12 in

 Length
 406.4 mm | 16 in

 Mounting Diameter 2, maximum
 228.6 mm | 9 in

 Mounting Diameter 2, minimum
 101.6 mm | 4 in

 Mounting Diameter, maximum
 88.9 mm | 3.5 in

 Mounting Diameter, minimum
 38.1 mm | 1.5 in

Material Specifications

Material Type Hot dip galvanized steel

#### Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 2

**Weight, net** 15.9 kg | 35.053 lb

### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



# MS-100-SSH

