MTC4015120H



H-Frame, 10ft long with 4 Posts (no ice canopy)

Product Classification

Product Type Ice canopies and shields

Dimensions

Height	4064 mm 160 in
Width	177.8 mm 7 in
Length	3048 mm 120 in

Material Specifications

Material TypeHot dip galvanized steel

Packaging and Weights

Included	Hardware	Legs	Unistrut
Packaging quantity	1		
Weight, net	265.1 kg	584.445	ō lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted
ISO	

Included Products

9001:2015

MF-130 – Direct Burial Pipe Column, 13 ft 4 in

Page 1 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 3, 2024



MF-130

Direct Burial Pipe Column, 13 ft 4 in

Product Classification

Product Type Pipe column

General Specifications

Application	Direct burial
Mounting	Waveguide bridge support bracket
Pipe, quantity	1

Dimensions


Height	4064 mm 160 in
Width	88.9 mm 3.5 in
Length	88.9 mm 3.5 in
Pipe Length	4,053.84 mm 159.6 in
Pipe Outer Diameter	88.9 mm 3.5 in

Page 2 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 15, 2023



Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Anchors | Pipe

Packaging quantity

45.8 kg | 100.972 lb

Regulatory Compliance/Certifications

1

Agency

Weight, net

Classification

Page 3 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 15, 2023



MF-130

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS



Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

Compliant/Exempted

Page 4 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 15, 2023

