

F4R-DMDR-3M-D

D-CLASS HELIAX® 1/2" Superflexible Fire retardant SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male Right angle, 3 m, with black non-halogenated fire retardant polyolefin jacket



Product Classification

| | |
|-----------------------|--------------------------------|
| Product Type | SureFlex® D-CLASS, dynamic PIM |
| Product Brand | HELIAX® SureFlex® |
| Product Series | RSJ4RK-50 |

General Specifications

| | |
|---|---------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Right angle |
| Interface, Connector A | 7-16 DIN Male |
| Interface, Connector B | 7-16 DIN Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|----------------|
| Length | 3 m 9.843 ft |
| Nominal Size | 1/2 in |

Logo Image

F4R-DMDR-3M-D



Electrical Specifications

| | |
|--|------------------------------------|
| 3rd Order IMD Dynamic | -116 dBm |
| 3rd Order IMD Dynamic Test Method | Two +43 dBm carriers per IEC 62037 |
| DTF, Connector A | -34 dB |
| DTF, Connector B | -32 dB |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) | VSWR, typical | Return Loss, typical (dB) |
|----------------|-------|------------------|---------------|---------------------------|
| 698–960 MHz | 1.083 | 28 | | |
| 1700–2200 MHz | 1.083 | 28 | | |
| 2200–2700 MHz | 1.135 | 24 | | |
| 3400–3800 MHz | | | 1.222 | 20 |

Jumper Assembly Sample Label

F4R-DMDR-3M-D



Environmental Specifications

| | |
|--|---|
| EN50575 CPR Cable EuroClass Fire Performance | B2ca |
| EN50575 CPR Cable EuroClass Smoke Rating | s1a |
| EN50575 CPR Cable EuroClass Droplets Rating | d1 |
| EN50575 CPR Cable EuroClass Acidity Rating | a1 |
| Immersion Test Method | Meets IEC 60529:2001, IP68 in mated condition |