

CB-12-27LH



Cable banding, 1/2 in x 27 in length with attached locking head, package contains 25 pieces

Product Classification

Product Type	Banding
Ordering Note	CommScope® standard product (Global)

General Specifications

Adapter Type	Adapter
Color	Black
Mounting	Round member

Dimensions

Width	12.7 mm 0.5 in
Length	0.686 m 2.25 ft
Material Thickness	1.524 mm 0.06 in

Material Specifications

Material Type	Heat-stabilized weather resistant acetal
----------------------	--

Mechanical Specifications

Tensile Force	1,112.055 N 250 lbf
----------------------	-----------------------

Environmental Specifications

Installation temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity	25
---------------------------	----