

ST-BSP30



Ballast Pole, 30 ft

- Bolt-together ballast tray foundation
- No digging required
- Removable step pegs
- Collar mounting

Product Classification

Regional Availability	North America
Product Type	Monopole
Ordering Note	ANDREW® non-standard product
Warranty	One year

General Specifications

Application	Multi-point telecommunications Point-to-point communications
Equipment Load Rating	18 in microwave reflector Omni antenna Telecommunications unit
Foundation	Non-penetrating above ground design with aggregate fill
Monopole Capability Type	Medium duty
Monopole Design	Round conical
Optional Accessories	Antenna mounts Cabinet mounts Removable step pegs Solar mounts

Dimensions

Height	9.144 m 30 ft
Mounting Diameter, maximum	266.7 mm 10.5 in
Mounting Diameter, minimum	160.02 mm 6.3 in
Base Area	8 ft x 8 ft

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating Test Method	TIA/EIA-222-G
--------------------------------	---------------

Packaging and Weights

ST-BSP30

Included Ballast tray | Ground tab | Hand holes | Lightning rod | Monopole | Safety climb systems | Safety-climb | Step pegs

Packaging quantity 1

Weight, net 306.3 kg | 675.275 lb

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines