

ST-ERR40



Embedded Railroad Pole, 40 ft

- Quick deploy embedment
- Rivet nut mounting

Product Classification

Product Type Monopole

General Specifications

Application Positive train control/Centralized traffic control (PTC/CTC communications)

Equipment Load Rating 24 in microwave reflector | Directional antenna | Telecommunications unit | Yagi antenna

Foundation Embedded

Monopole Capability Type Medium duty

Monopole Design Multi-sided

Optional Accessories Antenna mounts | Cabinet mounts | Removable step pegs | Solar mounts

Dimensions

Height 12.192 m | 40 ft

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Ground tab | Hand holes | Lightning rod | Monopole | Safety-climb | Step pegs

Packaging quantity 1