

HFE212-4SEB



HELIAX® Hybrid Cable Assembly, 2 power conductors 12 AWG Blue/Grey, 4-fiber, black jacket, aluminum armor

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Hybrid cable assembly
Product Brand	HELIAX®
Product Series	HFE
Ordering Note	CommScope® non-standard product

General Specifications

Conductors, quantity	2
Construction Type	Hybrid standard tail
Interface, Connector A	DLC
Interface Feature, connector A	Standard
Interface Body Style, connector A	Straight
Interface, Connector B	DLC
Interface Feature, connector B	Standard
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	4

Dimensions

Cable Assembly Length Range (m)	1 – 20
Diameter Over Jacket	14.25 mm 0.561 in
Center Conductor Gauge	12 AWG

Ordering Tree

HFE212-4SEB



Mechanical Specifications

Minimum Bend Radius 134.6 mm | 5.299 in

Minimum Bend Radius, furcation 30 mm | 1.181 in

Optical Specifications

Fiber Type G.657.A2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.5

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

HFE212-4SEB

Packaging and Weights

Cable weight 0.2 kg/m | 0.134 lb/ft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)