# 760249279 | HFTP-AM-S211-E



HFTP-AM Customer premises fiber wall outlet, one SC/APC pigtail, one SC/APC adapter with shutter

- Compact fiber wall outlet for use at the final fiber termination point in the customer premises
- Can be wall mounted and mounted on wall boxes with fixation points of 60mm
- Direct termination with field installable connectors
- Laser safe with in-built individual shutters

#### **Product Classification**

Regional Availability EMEA | North America

**Product Type** Fiber wall outlet

Product Series HFTP
Minimum Order Quantity 300

### General Specifications

ColorWhiteCover TypeScrew-onInterface TypeSC/APC

**Mounting** Wall mount

Total Ports, quantity

#### Dimensions

 Height
 105.156 mm | 4.14 in

 Width
 83.058 mm | 3.27 in

 Depth
 25.146 mm | 0.99 in

# Material Specifications

Material Type LSZH thermoplastic

## Optical Specifications

Fiber Mode Singlemode

## **Environmental Specifications**

Storage Temperature -30 °C to +60 °C (-22 °F to +140 °F)

COMMSCSPE®

# 760249279 | HFTP-AM-S211-E

**Relative Humidity** Up to 93%, non-condensing

Environmental Space Indoor

Packaging and Weights

Packaging quantity 10

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

