

FGSB-MSHS-H12



FiberGuide® Horizontal Straight Section, 4x24in, 12ft Length, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Straight section
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Black
Orientation	Horizontal
Section Type	Straight section

Dimensions

Height	101.6 mm 4 in
Width	609.6 mm 24 in
Length	3,657.6 mm 144 in
System Dimensions	102 mm x 610 mm (4 in x 24 in)

Material Specifications

Material Type	Engineering Thermoplastic
----------------------	---------------------------

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Packaging quantity	2
---------------------------	---

FGSB-MSHS-H12

Weight, net 5.953 kg | 13.124 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

