
### ZB-H8



Horizontal Z-bracket, 23 in, for 14 coaxial cable runs

#### **Product Classification**

Product Type Bracket kit

## General Specifications

Cable Runs, quantity 14

Hole, quantity 14

Mounting Walls

#### Dimensions

 Height
 50.8 mm | 2 in


 Width
 152.4 mm | 6 in

 Length
 584.2 mm | 23 in

 Hole Size
 3/4 in | 7/16 in

# ZB-H8

#### Outline Drawing



#### Material Specifications

Material Type Hot dip galvanized steel

#### Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

#### Packaging and Weights

**Included** Z-bracket

Packaging quantity 1

**Weight, net** 2.4 kg | 5.291 lb

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

Page 2 of 3



# ZB-H8

**UK-ROHS** 

Compliant



\* Footnotes

**Wind Rating** 

BWS-Base Wind Speed; FBC-Florida Building Code

