

FJ-2SM-015AN



HELIAX® Discrete tail, 2 single mode fiber, armored, Top: Ruggedized DLC with fiber weatherproof shroud at RRU. Bottom: Split LC for junction box connection

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Wireless Fiber Cable Assemblies
Product Brand	HELIAX®
Product Series	FJ
Ordering Note	CommScope® non-standard product

General Specifications


Construction Type	Direct fiber tail
Interface, Connector A	DLC
Interface Feature, connector A	Outdoor
Interface, Connector B	DLC
Jacket Color	Black
Total Fibers, quantity	2

Dimensions

Cable Assembly Length Range (m)	1 – 60
Diameter Over Jacket	6 mm 0.236 in

Ordering Tree

FJ-2SM-015AN



Optical Specifications

Fiber Type	G.657.A2
Insertion Loss, typical note	Insertion loss is measured at 1310 and 1550 nm
Insertion Loss, typical	0.5

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Outdoor

Packaging and Weights

Cable weight	48 kg/km 32.255 lb/kft
---------------------	--------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

FJ-2SM-015AN

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)