

NOVUX[™] CSC100 Compact Fiber Closure, splice only, no adapters, no splitters, mounting clips, black

- CommScope's new NOVUX[™] non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus[™] gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX[™] compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

This product will be discontinued on: August 3, 2023

Replaced By:

CSC3-M5A1A1BB000 NOVUX[™] CSC100 Compact Fiber Closure, splice only, no adapters, no splitters, mounting clips, black

Product Classification

Regional Availability	Asia EMEA Latin America North America	
Portfolio	CommScope®	
Product Type	Single-ended, rectangular fiber closure	
Product Brand	NOVUX™	
Product Series	CSC 100	

General Specifications

Cable Ports Quantity, total	3 round ports + 6 multi-out ports (12 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Pole Wall
Port Type	No adapter
Port, quantity	0
Splitter Type	No splitter

Page 1 of 5




Splitter, quantity	0
Dimensions	
Height	284 mm 11.181 in
Width	117 mm 4.606 in
Depth	77 mm 3.031 in


Page 2 of 5



Dimension Drawing








Port Configuration

Position	Cable diameter	
	mm	Inches
Feeder cable	≤14	≤ 0.55
Branch cable	≤12	≤ 0.47
Single drops	≤ 8 (flat cable: 8 x 4,5)	≤ 0.32 (flat cable: 0.32 x 0.18)
Dual drops	≤ 6,2	≤ 0.25

Ordering Tree





Environmental Specifications

Environmental Space	Outdoor
UV Resistance	UV stabilized

Packaging and Weights

001.2015

12

Included	Mounting hardware
Packaging quantity	1
Packaging Type	Box Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
TL 9000:2016 (R6)	Compliant to this quality management practice
UK-ROHS	Compliant





Page 5 of 5

