


# FST-HS-48

---



FST Fiber Optic Splice Tray, 48 splice capacity

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber splice tray

## General Specifications

<b>Application</b>	For use with FDF splice panels
<b>Color</b>	Black
<b>Location of Manufacturing</b>	Waived per BABA waiver for BEAD Program
<b>Splicing Capacity, maximum</b>	48
<b>Splicing Type</b>	Heat shrink

## Environmental Specifications

<b>Storage Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
----------------------------	--------------------------------------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

