


FST-HS



FST Fiber Optic Splice Tray 12 splice capacity

Product Classification

Regional Availability	North America
Product Type	Fiber splice tray

General Specifications

Application	For use with FDF splice panels
Color	Black
Splicing Capacity, maximum	12
Splicing Type	Heat shrink

Environmental Specifications

Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
----------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

