## NG4-CMDKOGR



# NG4access® Cabled Module, singlemode LC/UPC to stub, 72 fiber, rollable ribbon, indoor/outdoor

- Cabled modules enable the routing of fiber cable to the frame, where multiple connectors are terminated to the frame with a single click
- Integrated connectors ensure the cables are kept in sequential order, and help prevent accidental fiber breakage or disruption to adjacent fibers during installation
- Available in a pigtail version for splicing on frame or preterminated to 24-fiber microcable or conventional IFC cable

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber cabled module

Product Brand NG4access®

Product Series NG4

Ordering Note For fiber modules with custom cable lengths, please contact your local CommScope

representative

#### General Specifications

**Configuration Type** NG4 Module to Stub tail

Adapters, quantity, front 36

**Body Style** Straight orientation

Cable Color Yellow

 Cable Type
 Indoor/outdoor - Rollable Ribbon

Color, frontBlackColor, housingBlackColor, rearBlackInterface, frontLC/UPCInterface, rearStub tail

**Polarity** Pairs, straight

Total Fibers, quantity 72

Total Ports, quantity, front 72



# NG4-CMDKOGR


#### **Dimensions**

 Height
 13.3 mm | 0.524 in

 Width
 159.9 mm | 6.295 in

 Depth
 101 mm | 3.976 in

#### Ordering Tree



#### Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2

### **Environmental Specifications**

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Packaging and Weights

Packaging quantity

**COMMSCOPE®** 

# NG4-CMDKOGR

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

