760252934 | 26" Pole Cab with Round Tapered Pole

Bottom of the Pole, 26in Square base with round tapered shaft 4G/5G/mmWave Concealment Enclosure to house and conceal multiple low to high power radios and other wireless infrastructure equipment in a cabinet at the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of
- Flexible configuration accepts low to high-power single or dual band radios, Integrated AC load center/OVP and Disconnect and integrated AC/DC rectifier options

Supports 4G and mmWave/5G mounting, luminaire arms.

OBSOLETE

Product Classification

Portfolio CommScope®

Product Type Pole cab **Product Brand** Metro Cell

Ordering Note CommScope® standard product with terms

Warranty One year

General Specifications

Color Light Gray (RAL 7035)

Color Options Beige-Grey (RAL 7006) | Black (RAL 9005) | Black Green (RAL 6012) | Brown (RAL 8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Umbra Grey (RAL 7022)

Poured Concrete | Pre-Cast Concrete **Compatible Foundation Type**

Cameras | Digital Signage | Emergency Call Station | Environmental **Compatible Smart Devices**

Monitoring | Security Lighting | WIFI

Cooling Fan Cooling

Power Supply Compatibility ABB CC1600 | CCI PSU-1200W-48-N | DELTA 2.0 | PSU-AC-08

(1) 8843/4449 dual-band high power radio and (2) PSU-AC08 | (2) RRUS11/12/32, 2212, Radio Compatibility, Ericsson

4415, 4426, 4478 (base) | (3) 2203/2205/2208 (Pole Top) | 220x | 440x | Power

Distribution

Radio Compatibility, Nokia (2) Airscale dual band radios (160W or 320W and (2) Delta 1kW rectifiers

(base) | AHFIA | AHFIB | AHIA | AHIB | AHLBA | AHLBBA | AZRB | Airscale

micro | Power Distribution

Radio Compatibility Samsung DELTA 2.0 | GE | Power Distribution | RF4402D-D1A | RT2201-46A | RT4401-48A

Page 1 of 2

760252934 | 26" Pole Cab with Round Tapered Pole

Radios Included None

Dimensions

Height Note 4 ft tall Equipment Cabinet Base

Pole Height Options 10.668 m | 35 ft | 9.144 m | 30 ft

 Width
 660.4 mm | 26 in

 Depth
 660.4 mm | 26 in

Depth Note Square

Pole Diameter 203.2 mm | 8 in

Electrical Specifications

Power/Fiber Input AC load center with OVP and disconnect

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Steel

Environmental Specifications

Thermal Compliance GR-487

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

Pole Height Options Overall AGL Standard Height