

SSC-760236114E5 | Radio Enclosure Pico for Ericsson Radios



Middle of Pole Pico Concealment Enclosure for 4455, 4435, and 220x/440x radios

- Intended to be used with remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

Accommodates (1) 4435, and (1) 4455 with the separately ordered "860665179-AMK-003" kit

Product Classification

Product Type	Mid pole
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022) White (RAL 9010)
Cooling	Passive Cooling
Mounting Options	Non-tapered poles Tapered poles Wood poles
Radio Compatibility, Ericsson	(1) 4455 and up to (2) 220x/440x 220x 440x 4435 4455
Radios Included	None

Dimensions

Height	1016 mm 40 in
Width	401.32 mm 15.8 in
Depth	304.8 mm 12 in

Electrical Specifications

Power/Fiber Input	Trade size knockouts at rear side
--------------------------	-----------------------------------

Material Specifications

SSC-760236114E5 | Radio Enclosure Pico for Ericsson Radios

Finish Aluminum	Chromate
Finish Concealment Covers	Powder coated
Material Type	Aluminum Steel

Environmental Specifications

Thermal Compliance	GR-487
---------------------------	--------

Packaging and Weights

Volume	0.125 m ³ 4.4 ft ³
Weight (loaded)	36.287 kg 80 lb
Weight (unloaded)	18.144 kg 40 lb