


# L-ZT

---



Fiber Optic Cable, Indoor Zero Halogen, CPR-only flame rated, Duplex Zip Cord


## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   Latin America   Middle East/Africa   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor cable
<b>Product Series</b>	L-ZT

## General Specifications

<b>Cable Type</b>	MPO trunk cable
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-free

## Representative Image



## Environmental Specifications

# L-ZT

---

<b>Installation temperature</b>	-0 °C to +60 °C (-32 °F to +140 °F)
<b>Operating Temperature</b>	-4 °C to +60 °C (-14 °F to +140 °F)
<b>Storage Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Cable Qualification Standards</b>	ANSI/ICEA S-83-596   Telcordia GR-409
<b>Environmental Space</b>	Plenum

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable