



Propel 4RU sliding tray fiber panel, accepts Propel ULL modules or adapter packs, providing up to 288 duplex LC ports, 288 MPO ports or 576 SN ports (1152f)

- Any size Propel component can be used in each panel or blade
- Components can be installed and removed from front or rear of panel
- Supports 8f, 12f, 16f and 24f applications while maintaining full panel density
- Cable mounting system allows for multiple trunk cables to be securely attached in the rear of panel

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Brand	Propel
Product Series	PPL

General Specifications

Color	Gray
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	4
Shelf Movement	Sliding
Total Ports, quantity	0

Dimensions

Height	178 mm 7.008 in
Width	483 mm 19.016 in
Depth	470 mm 18.504 in

Port Configuration

Panel size	8-fiber components	12-fiber components	16-fiber components	24-fiber components
1RU	up to 6 per blade	up to 4 per blade	up to 3 per blade	up to 2 per blade
2RU	up to 6 per blade	up to 4 per blade	up to 3 per blade	up to 2 per blade
4RU	up to 6 per blade	up to 4 per blade	up to 3 per blade	up to 2 per blade
Each blade has 12 lanes				
	Requires 2 lanes	Requires 3 lanes	Requires 4 lanes	Requires 6 lanes

Material Specifications

Material Type Steel

Environmental Specifications

Safety Standard c-UL-us

Packaging and Weights

Packaging quantity 1

Weight, net 14.742 kg | 32.5 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

