



Angle Adapter, compact 1/4 in tapped hole

## Product Classification

<b>Product Type</b>	Adapter
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Adapter Type</b>	Angle adapter
<b>Mounting</b>	1/4 in tapped hole

## Dimensions

<b>Inside Width</b>	16.51 mm   0.65 in
<b>Outside Width</b>	21.59 mm   0.85 in
<b>Inside Length</b>	16.002 mm   0.63 in
<b>Outside Length</b>	44.45 mm   1.75 in
<b>Material Thickness</b>	2.337 mm   0.092 in

## Material Specifications

<b>Material Type</b>	Zinc-plated steel
----------------------	-------------------

## Mechanical Specifications

<b>Installation Torque, maximum</b>	12 ft lb   16.27 N-m
<b>Installation Torque, minimum</b>	10 ft lb   13.558 N-m
<b>Maximum Loading</b>	Single, 1-5/8 in cable

## Packaging and Weights

<b>Height, packed</b>	2.5 cm   0.984 in
-----------------------	-------------------

# 209821

---

<b>Width, packed</b>	12.7 cm   5 in
<b>Length, packed</b>	20.3 cm   7.992 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.69 kg   1.521 lb

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

REACH-SVHC

ROHS

### Classification

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

