

F1-BSFNM-M5-HF

FSJ1-50A SureFlex® Jumper with interface types N Male and SMA Female Bulkhead, 0.5 Meters



Product Classification

Product Type	Wireless transmission cable assembly
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Bulkhead
Interface, Connector A	N Male
Interface, Connector B	SMA Female
Specification Sheet Revision Level	A

Dimensions

Length	0.5 m 1.64 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
10–18000 MHz	1.577	13

Jumper Assembly Sample Label

F1-BSFNM-M5-HF



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition