

# SSC-760233122X6 | 18 in Pole Top for C-Band



## Top of Pole 18in Dia Concealment Enclosure for C-Band and power supply

- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures

Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your ANDREW Representative for exact model number.

Mounts directly to ANDREW poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

### ERICSSON VERSION:

- Supports Ericsson C-Band 8863 with 6302 power supply
- Supports 4415 OR 4426 OR 4478 plus AC08 power supply with separately ordered "860662724-C03" bracket kit

### SAMSUNG VERSION:

- Support of Samsung RT8808 and Delta 2.0 or ABB power supply

### ANTENNA MOUNTS per COMPATIBILITY CHART

- Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket plus PT18-K-xx Antenna Mount

## Product Classification

<b>Product Type</b>	Pole top
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	ANDREW® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antenna Compatibility, ANDREW</b>	ANDREW Canister Antennas
<b>Antenna Compatibility, Other Vendors</b>	ACE   AMPHENOL   GALTRONICS   GAMMA NU   JMA   KATHREIN   KMW   ROSENBERGER
<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Black (RAL 9005)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver
<b>Cooling</b>	Passive Cooling
<b>Mounting Options</b>	Concrete poles   Fluted poles   Metal poles   Non-tapered poles   Tapered poles   Wood poles

# SSC-760233122X6 | 18 in Pole Top for C-Band

---

**Power Supply Compatibility** 6302 | ABB CC1600 | DELTA 2.0 | PSU-AC-08

**Radio Compatibility, Ericsson** 4415 | 4426 | 4478 | 8863

**Radio Compatibility Samsung** RT8808-77A

**Radios Included** None

## Dimensions

**Height** 812.8 mm | 32 in

**Width** 457.2 mm | 18 in

**Depth** 457.2 mm | 18 in

**Mounting Bolt Circle Diameter** 142.748 mm | 5.62 in | 241.3 mm | 9.5 in

## Material Specifications

**Finish Aluminum** Chromate

**Finish Concealment Covers** Powder coated

**Material Type** Aluminum | Steel

## Environmental Specifications

**Thermal Compliance** GR-487

## Packaging and Weights

**Volume** 0.134 m<sup>3</sup> | 4.72 ft<sup>3</sup>

**Weight (unloaded)** 34.019 kg | 75 lb