

BTT

Base Product



BTT Fiber Access Hardened Terminal, Optical Taps, factory-sealed

- Full and terminating tap versions
- Available in both butt and Inline configurations
- Available in both black and gray housing color
- Color coded ports for identification easiness

Product Classification

Regional Availability	Europe Latin America
Product Type	Access terminal, with tap
Product Series	BTT
Minimum Order Quantity	1

General Specifications

Cable Type	No cable (stubless)
Distribution Type	8-port tap
Drop Port Type	Hardened full-size SC/APC
Enclosure Color	Black
Forward Port Type	Hardened full-size SC/APC adapter
Forward Port, quantity	1
Input Tap, quantity	1
Mounting	Handhole Pedestal Pole
Port Type	Hardened full-size SC/APC
Splitter, quantity	1
Stub Type	No tail

Dimensions

Width	141 mm 5.551 in
Depth	90 mm 3.543 in
Length	258 mm 10.157 in
Cable Length, stub	0 ft (0 m)

Material Specifications

Enclosure Material Type Glass filled polypropylene (GF-PP)

Optical Specifications

Fiber Type G.657.A2

Operating Wavelength Range 1260 – 1650 nm

Environmental Specifications

Operating Temperature -30 °C to +70 °C (-22 °F to +158 °F)

Relative Humidity 0%–100%, condensing

Environmental Space Above ground | Below ground | Buried

UV Resistance UV stabilized

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

