

MC-PK10-B



Low-Profile Co-location Platform Base Kit, 10.5 ft face, for 12in to 50in OD Monopoles, No Pipes or Support Rail

Product Classification

Product Type Monopole platform kit

General Specifications

Mounting Monopole, 304.8–1270 mm (12–50 in) OD

Pipe, quantity 0

Sectors, quantity 3

Dimensions

Height 292.1 mm | 11.5 in

Face Width 3.2 m | 10.5 ft

Width 3,200.4 mm | 126 in

Face Support Pipe Diameter 88.9 mm | 3.5 in

Mounting Diameter, maximum 1,270 mm | 50 in

Mounting Diameter, minimum 304.8 mm | 12 in

Pipe Outer Diameter 0 mm | 0 in

Stand-off Distance 914.4 mm | 36 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Platform | Ring mount

Packaging quantity 1

MC-PK10-B

Weight, net 412.315 kg | 909 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code